



### XT200M3H

h(m)	MF 0.80			
	Xa	Xb	Yb	Ya
2,0	3.11	7.53	7.50	3.29
2,5	3.35	8.34	8.37	3.49
3,0	3.48	8.98	8.93	3.62
3,5	3.51	9.47	9.37	3.68
4,0	3.47	9.79	9.70	3.65
4,5	3.35	10.00	9.93	3.53
5,0	3.17	10.08	10.06	3.34
5,5	2.90	10.03	10.01	3.07
6,0	2.53	9.86	9.82	2.67
6,5	1.97	9.60	9.55	2.12
7,0	0.98	9.23	9.17	1.15

### XT201M3H

h(m)	MF 0.80			
	Xa	Xb	Yb	Ya
2,0	3.24	7.98	5.04	2.05
2,5	3.56	8.71	5.38	2.34
3,0	3.77	9.35	5.87	2.60
3,5	3.90	9.98	6.48	2.80
4,0	3.99	10.43	7.02	2.94
4,5	4.04	10.80	7.48	3.04
5,0	4.01	11.05	7.87	3.10
5,5	3.92	11.24	8.17	3.04
6,0	3.72	11.34	8.41	2.69
6,5	3.43	11.36	8.58	2.25
7,0	2.96	11.28	8.54	1.69
7,5	2.41	11.10	8.25	1.16
8,0	1.49	10.80	7.84	0.81