

# Female to female thread coupler



## Features

- Straight through female to female coupler

## Approvals



## Certification & Standards

<b>Approved to:</b>	IEC EN 60079-0, 60079-1, 60079-7, 60079-31
<b>EC TYPE Examination Certificate:</b>	ATEX: BASEFFA08ATEX0359U IECEX: IECEX BAS 08.0121U Ex e IIC Gb Ex tb IIIC Db
<b>Safe operating temperature range:</b>	-60°C to +200°C

Part No.	Metric Thread Size (mm)	Part No.	Metric Thread Size (mm)	Part No.	Metric Thread Size (mm)
<b>Nickel Plated</b>		<b>Brass</b>		<b>Stainless Steel</b>	
EXN/M16/C	16	EX/M16/C	16	EXS/M16/C	16
EXN/M20/C	20	EX/M20/C	20	EXS/M20/C	20
EXN/M25/C	25	EX/M25/C	25	EXS/M25/C	25
EXN/M32/C	32	EX/M32/C	32	EXS/M32/C	32
EXN/M40/C	40	EX/M40/C	40	EXS/M40/C	40
EXN/M50/C	50	EX/M50/C	50	EXS/M50/C	50
EXN/M63/C	63	EX/M63/C	63	EXS/M63/C	63
EXN/M75/C	75	EX/M75/C	75	EXS/M75/C	75

Part No.	NPT Thread Size (inch)	Part No.	NPT Thread Size (inch)	Part No.	NPT Thread Size (inch)
<b>Nickel Plated</b>		<b>Brass</b>		<b>Stainless Steel</b>	
EXN/038/C	3/8	EX/038/C	3/8	EXS/038/C	3/8
EXN/050/C	1/2	EX/050/C	1/2	EXS/050/C	1/2
EXN/075/C	3/4	EX/075/C	3/4	EXS/075/C	3/4
EXN/100/C	1	EX/100/C	1	EXS/100/C	1
EXN/125/C	1 1/4	EX/125/C	1 1/4	EXS/125/C	1 1/4
EXN/150/C	1 1/2	EX/150/C	1 1/2	EXS/150/C	1 1/2
EXN/200/C	2	EX/200/C	2	EXS/200/C	2
EXN/250/C	2 1/2	EX/250/C	2 1/2	EXS/250/C	2 1/2

