

EXLB - General Use PVC Conduit

Ex e LT Metallic Range



Material

- PVC Covering
- Galvanised Steel Core
- Cotton Packed (03-07)
- Interlocked (08-09)

Features

- Oil Resistant
- Flame Retardant
- Can be used with Ex LT Fittings for Ex e Systems or combination Ex LT and HA-G1 Fittings for Ex d e Systems

Approvals



Certification & Standards

Approved to:	EN/IEC 60079-0, 60079-7, 60079-31 IEC 61386-1, 61386-23
Type Examination Certificates:	For use with Ex LT Fittings and HA-G1: Baseefa 15 ATEX 0175X, IECEx BAS 15.0130X Ex eb IIC Gb Ex tb IIC Db
Temperature:	Certified -20°C to +70°C Static -25°C to +105°C Dynamic -5°C to + 105°C

Compatible with: EXQ*, EXS*, EXR*, HA-G1 Fittings / Colour: Black

Part No.	Conduit Size		Static Bend Radius (mm)	Inside Diameter (mm)	Coil Length (m)	GiD Codes
	Metric (mm)	US Trade (Inch)				
EXLB03*	16	3/8"	50.0	12.5	10 / 30	7TCA297120R0066 - 7TCA297120R0067
EXLB04*	20	1/2"	80.0	16.0	10 / 30	7TCA297120R0069 - 7TCA297120R0070
EXLB05*	25	3/4"	110.0	21.0	10 / 30	7TCA297120R0073 - 7TCA297120R0074
EXLB06*	32	1"	145.0	26.4	10 / 20	7TCA297120R0076 - 7TCA297120R0077
EXLB07*	40	1-1/4"	180.0	35.3	10 / 20	7TCA297120R0078 - 7TCA297120R0079
EXLB08*	50	1-1/2"	240.0	40.4	10 / 20	7TCA297120R0080 - 7TCA297120R0081
EXLB09*	63	2"	345.0	51.6	10 / 20	7TCA297120R0082 - 7TCA297120R0083

*Add coil length to complete part number e.g. 10 metres = EXLB10