

# EXQ - Metric Straight Fitting

## LT Metallic Range



### Material

- Nickel Plated Brass
- Brass Seal
- Silicone O'ring
- Nylon Anti-Abrasion Throat

### Features

- Metallic Fitting for use with Liquid Tight Conduit
- Ex eb Ex tb Approved
- Suitable for use in zones 1, 2, 21 and 22

### Approvals



### Certification & Standards

Approved to:	EN/IEC 60079-0, 60079-7, 60079-31 IEC 61386 Compliant
Type Examination Certificates:	<b>For use with Ex LT Conduits</b> Baseefa 15 ATEX 0175X, IECEx BAS 15.0130X Ex eb IIC Gb Ex tb IIC Db
Temperature:	EX*HC -35°C to +105°C EX*T -20°C to +70°C EX*B -20°C to +70°C EX*UB -20°C to +70°C

Compatible with: EX\*B, EX\*T, EX\*HC, EX\*UB Conduits / Colour: Nickel Plated Brass

Part No.	Conduit Size		Thread Metric	Length (mm)	Across Flats (mm)	GID Codes
	Metric (mm)	US Trade (Inch)				
EXQM0303	16	3/8"	M16x1.5	21.0	25.4	7TCA297120R0191
EXQM0304	16	3/8"	M20x1.5	21.0	25.4	7TCA297120R0192
EXQM0404	20	1/2"	M20x1.5	22.0	28.5	7TCA297120R0193
EXQM0505	25	3/4"	M25x1.5	25.0	35.0	7TCA297120R0194
EXQM0606	32	1"	M32x1.5	30.0	42.0	7TCA297120R0195
EXQM0707	40	1-1/4"	M40x1.5	38.0	52.0	7TCA297120R0196
EXQM0808	50	1-1/2"	M50x1.5	41.0	60.0	7TCA297120R0197
EXQM0909	63	2"	M63x1.5	46.0	70.0	7TCA297120R0198

\*Fittings also available in Stainless Steel