

# EXQ - NPT Straight Fitting

## LT Metallic Range



### Material

- Nickel Plated Brass
- Brass Conduit Seal
- Silicone O'ring Thread Seal
- Nylon Anti-Abrasion Cable Protector

### Features

- Metallic Fitting for use with Liquid Tight Conduit
- Ex eb Ex tb Approved
- Suitable for use in zones 1, 2, 21 and 22

### Approvals



### Certification & Standards

Approved to:	EN/IEC 60079-0, 60079-7, 60079-31 IEC 61386 Compliant
Type Examination Certificates:	<b>For use with Ex LT Conduits</b> Baseefa 15 ATEX 0175X, IECEx BAS 15.0130X Ex eb IIC Gb Ex tb IIC Db
Temperature:	EX*HC -35°C to +105°C EX*T -20°C to +70°C EX*B -20°C to +70°C EX*UB -20°C to +70°C

Compatible with: EX\*B, EX\*T, EX\*HC, EX\*UB Conduits / Colour: Nickel Plated Brass

Part No.	Conduit Size		Thread NPT	Length (mm)	Across Flats (mm)	GID Codes
	Metric (mm)	US Trade (Inch)				
EXQA0304	16	1/2"	1/2"	21.0	25.4	7TCA297120R0175
EXQA0404	20	1/2"	1/2"	22.0	28.5	7TCA297120R0176
EXQA0505	25	3/4"	3/4"	25.0	35.0	7TCA297120R0177
EXQA0606	32	1"	1"	30.0	42.0	7TCA297120R0178
EXQA0707	40	1-1/4"	1-1/4"	38.0	52.0	7TCA297120R0179
EXQA0808	50	1-1/2"	1-1/2"	41.0	60.0	7TCA297120R0180
EXQA0909	63	2"	2"	46.0	70.0	7TCA297120R0181

\*Fittings also available in Stainless Steel