

EXR - Metric 45° Elbow Fitting

LT Metallic Range



Material

- Nickel Plated Brass
- Brass Conduit Seal
- Silicone O'ring Thread Seal
- Nylon Anti-Abrasion Cable Protector

Features

- Metallic Fitting for use with Liquid Tight Conduit
- Ex eb Ex tb Approved
- Suitable for use in zones 1, 2, 21 and 22

Approvals



Certification & Standards

Approved to:	EN/IEC 60079-0, 60079-7, 60079-31 IEC 61386 Compliant
Type Examination Certificates:	For use with Ex LT Conduits Baseefa 15 ATEX 0175X, IECEx BAS 15.0130X Ex eb IIC Gb Ex tb IIC Db
Temperature:	EX*HC -35°C to +105°C EX*T -20°C to +70°C EX*B -20°C to +70°C EX*UB -20°C to +70°C

Compatible with: EX*B, EX*T, EX*HC, EX*UB Conduits / Colour: Nickel Plated Brass

Part No.	Conduit Size		Thread Metric	Length (mm)	Across Flats (mm)	GID Codes
	Metric (mm)	US Trade (Inch)				
EXRM0303	16	3/8"	M16x1.5	54.0	25.4	7TCA297120R0472
EXRM0304	16	3/8"	M20x1.5	55.0	25.4	7TCA297120R0216
EXRM0404	20	1/2"	M20x1.5	58.0	28.5	7TCA297120R0217
EXRM0505	25	3/4"	M25x1.5	65.6	35.0	7TCA297120R0218
EXRM0606	32	1"	M32x1.5	85.0	42.0	7TCA297120R0219
EXRM0707	40	1-1/4"	M40x1.5	93.8	52.0	7TCA297120R0220
EXRM0808	50	1-1/2"	M50x1.5	106.5	60.0	7TCA297120R0221
EXRM0909	63	2"	M63x1.5	125.0	70.0	7TCA297120R0222

*Fittings also available in Stainless Steel