

EXR - NPT 45° Elbow Fitting

LT Metallic Range



Material

- Nickel Plated Brass
- Brass Conduit Seal
- Silicone O'ring Thread Seal
- Nylon Anti-Abrasion Cable Protector

Features

- Metallic Fitting for use with Liquid Tight Conduit
- Ex eb Ex tb Approved
- Suitable for use in zones 1, 2, 21 and 22

Approvals



Certification & Standards

Approved to:	EN/IEC 60079-0, 60079-7, 60079-31 IEC 61386 Compliant
Type Examination Certificates:	For use with Ex LT Conduits Baseefa 15 ATEX 0175X, IECEx BAS 15.0130X Ex eb IIC Gb Ex tb IIC Db
Temperature:	EX*HC -35°C to +105°C EX*T -20°C to +70°C EX*B -20°C to +70°C EX*UB -20°C to +70°C

Compatible with: EX*B, EX*T, EX*HC, EX*UB Conduits / Colour: Nickel Plated Brass

Part No.	Conduit Size		Thread NPT	Length (mm)	Across Flats (mm)	GID Codes
	Metric (mm)	US Trade (Inch)				
EXRA0304	16	1/2"	1/2"	55.0	25.4	7TCA297120R0209
EXRA0404	20	1/2"	1/2"	58.0	28.5	7TCA297120R0210
EXRA0505	25	3/4"	3/4"	65.6	35.0	7TCA297120R0211
EXRA0606	32	1"	1"	85.0	42.0	7TCA297120R0212
EXRA0707	40	1-1/4"	1-1/4"	93.8	52.0	7TCA297120R0213
EXRA0808	50	1-1/2"	1-1/2"	106.5	60.0	7TCA297120R0214
EXRA0909	63	2"	2"	125.0	70.0	7TCA297120R0215

*Fittings also available in Stainless Steel