


**IEC SYSTEM FOR MUTUAL RECOGNITION OF TEST CERTIFICATES FOR ELECTRICAL EQUIPMENT
(IECEE) CB SCHEME****CB TEST CERTIFICATE**

| | |
|---|---|
| Product | Enclosures for fixed installation for protective devices and power dissipating equipments |
| Name and address of the applicant | ABB S.p.A. Via Vittor Pisani, 16 20124 – Milano Italy |
| Name and address of the manufacturer | ABB BULGARIA EOOD Rakovski Branch Bldg 1 Industrial Road 1 14 4142 Stryama Village Bulgaria |
| Name and address of the factory | <input type="checkbox"/> Additional information on page 2 ABB BULGARIA EOOD Rakovski Branch Bldg 1 Industrial Road 1 14 4142 Stryama Village Bulgaria |
| Note: When more than one factory, please report on page 2 | |
| Ratings and principal characteristics | Flush-mounting enclosures; -25 °C to +60 °C; IP40; rated insulation voltage = 400 V (see also pages 4 and from 21 to 23 of Test Report MI16-0013798-01 and Additional Sheet) |
| Trademark (if any) |  ABB |
| Customer's Testing Facility (CTF) Stage used | |
| Model / Type Ref. | Series BREVA (see Additional Sheet) |
| Additional information (if necessary may also be reported on page 2) | <input type="checkbox"/> Additional information on page 2 |
| A sample of the product was tested and found to be in conformity with | IEC 60670-1:2002, IEC 60670-1:2002/AMD1:2011, IEC 60670-24:2011 |
| As shown in the Test Report Ref. No. which forms part of this Certificate | MI16-0013798-02 |

This CB Test Certificate is issued by the National Certification Body

IMQ S.p.A.
Via Quintiliano 43, IT-I-20138 Milano, Italy



Description of flush-mounting enclosures series BREVA

| Type reference | Description | Dimensions W × H × D (mm) | Number of modules (number of DIN rail guides) | Maximum capability to dissipate power (W) |
|-----------------|----------------------------|------------------------------|--|--|
| 626-026022-002 | With blind white door | 120 × 180 × 102 | 2 (1) | 13 |
| 1SZR004001A1100 | | | | |
| BEF401102 | | | | |
| 1SZR004002A1100 | | | | |
| BEF401202 | | | | |
| 626-026302-002 | With transparent grey door | | | |
| 1SZR004001A1200 | | | | |
| BEF402102 | | | | |
| 1SZR004002A1200 | | | | |
| BEF402202 | | | | |
| 626-026022-004 | With blind white door | 155 × 180 × 102 | 4 (1) | 17 |
| 1SZR004001A1101 | | | | |
| BEF401104 | | | | |
| 1SZR004002A1101 | | | | |
| BEF401204 | | | | |
| 626-026302-004 | With transparent grey door | | | |
| 1SZR004001A1201 | | | | |
| BEF402104 | | | | |
| 1SZR004002A1201 | | | | |
| BEF402204 | | | | |
| 626-026022-006 | With blind white door | 190 × 180 × 102 | 6 (1) | 19 |
| 1SZR004001A1102 | | | | |
| BEF401106 | | | | |
| 1SZR004002A1102 | | | | |
| BEF401206 | | | | |
| 626-026302-006 | With transparent grey door | | | |
| 1SZR004001A1202 | | | | |
| BEF402106 | | | | |
| 1SZR004002A1202 | | | | |
| BEF402206 | | | | |

Description of flush-mounting enclosures series BREVA

| Type reference | Description | Dimensions W × H × D (mm) | Number of modules (number of DIN rail guides) | Maximum capability to dissipate power (W) |
|-----------------|----------------------------|------------------------------|--|--|
| 626-026022-008 | With blind white door | 230 × 180 × 102 | 8 (1) | 23 |
| 1SZR004001A1103 | | | | |
| BEF401108 | | | | |
| 1SZR004002A1103 | | | | |
| BEF401208 | | | | |
| 626-026302-008 | With transparent grey door | | | |
| 1SZR004001A1203 | | | | |
| BEF402108 | | | | |
| 1SZR004002A1203 | | | | |
| BEF402208 | | | | |
| 626-026022-012 | With blind white door | 300 × 220 × 102 | 12 (1) | 30 |
| 1SZR004001A1104 | | | | |
| BEF401112 | | | | |
| 1SZR004002A1104 | | | | |
| BEF401212 | | | | |
| 626-026302-012 | With transparent grey door | | | |
| 1SZR004001A1204 | | | | |
| BEF402112 | | | | |
| 1SZR004002A1204 | | | | |
| BEF402212 | | | | |
| 626-026022-016 | With blind white door | 230 × 315 × 102 | 16 (2) | 34 |
| 1SZR004001A1105 | | | | |
| BEF401116 | | | | |
| 1SZR004002A1105 | | | | |
| BEF401216 | | | | |
| 626-026302-016 | With transparent grey door | | | |
| 1SZR004001A1205 | | | | |
| BEF402116 | | | | |
| 1SZR004002A1205 | | | | |
| BEF402216 | | | | |

Description of flush-mounting enclosures series BREVA

| Type reference | Description | Dimensions W × H × D (mm) | Number of modules (number of DIN rail guides) | Maximum capability to dissipate power (W) |
|-----------------|----------------------------|------------------------------|--|--|
| 626-026022-024 | With blind white door | 300 × 355 × 102 | 24 (2) | 37 |
| 1SZR004001A1107 | | | | |
| BEF401124 | | | | |
| 1SZR004002A1107 | | | | |
| BEF401224 | | | | |
| 626-026302-024 | With transparent grey door | | | |
| 1SZR004001A1207 | | | | |
| BEF402124 | | | | |
| 1SZR004002A1207 | | | | |
| BEF402224 | | | | |
| 626-026022-036 | With blind white door | 300 × 450 × 155 | 36 (3) | 43 |
| 1SZR004001A1109 | | | | |
| BEF401136 | | | | |
| 1SZR004002A1109 | | | | |
| BEF401236 | | | | |
| 626-026302-036 | With transparent grey door | | | |
| 1SZR004001A1209 | | | | |
| BEF402136 | | | | |
| 1SZR004002A1209 | | | | |
| BEF402236 | | | | |