

## PRODUCT-DETAILS

# ACS355-03E-15A6-4+B063

ACS355-03E-15A6-4+B063 PN:7.5KW 15.6A



## General Information

|                         |  |
|-------------------------|--|
| Global Commercial Alias | ACS355-03E-15A6-4+B063   |
| Product ID              | 3ABD0000058129   |
| ABB Type Designation    | ACS355-03E-15A6-4+B063   |
| Catalog Description     | ACS355-03E-15A6-4+B063 PN:7.5KW 15.6A  |
| Long Description        | The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications. The drive are user-friendly, yet provide a wide range of built-in technology, such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors. |

## Ordering

|                         |                                       |
|-------------------------|---------------------------------------|
| Country of Origin       | China (CN)                            |
| Customs Tariff Number   | 85044099                              |
| Invoice Description     | ACS355-03E-15A6-4+B063 PN:7.5KW 15.6A |
| Made To Order           | No                                    |
| Minimum Order Quantity  | 1 piece                               |
| Order Multiple          | 1 piece                               |
| Quote Only              | No                                    |
| Selling Unit of Measure | piece                                 |

| Dimensions                     |          |
|--------------------------------|----------|
| Product Net Weight             | 13 kg    |
| Product Net Depth / Length     | 277 mm   |
| Product Net Height             | 436 mm   |
| Product Net Width              | 246 mm   |
| Package Level 1 Depth / Length | 330 mm   |
| Package Level 1 Height         | 220 mm   |
| Package Level 1 Width          | 205 mm   |
| Package Level 1 Units          | 0 carton |

| Technical        |     |
|------------------|-----|
| Frame Size       | R3  |
| Efficiency Level | IE2 |

| Additional Information |                     |
|------------------------|---------------------|
| Product Name           | FREQUENCY CONVERTER |

| Classifications |          |
|-----------------|----------|
| UNSPSC          | 39122001 |

| Environmental |  |
|---------------|--|
| WEEE Category | 5. Small Equipment (No External Dimension More Than 50 cm) |

| Categories   |  |
|--|--|
| Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive |  |

