



PRODUCT-DETAILS

ACS880-04-715A-5

ACS880-04-715A-5 PN: 500KW, IN: 715A

General Information

Global Commercial Alias	ACS880-04-715A-5
Product ID	3ABD0000139079
ABB Type Designation	ACS880-04-715A-5
Catalog Description	ACS880-04-715A-5 PN: 500KW, IN: 715A
Long Description	ACS880-04-715A-5

Additional Information

ABB Type Designation	ACS880-04-715A-5
CN8	85044090
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R11
Global Commercial Alias	ACS880-04-715A-5
Gross Weight	264 kg
Invoice Description	ACS880-04-715A-5 PN: 500KW, IN: 715A
IP Class	IP21
Made To Order	No
Medium Description	ACS880-04-715A-5 PN: 500KW, IN: 715A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	2050 mm
Package Level 1 Gross Weight	264 kg
Package Level 1 Height	690 mm
Package Level 1 Units	1 carton
Package Level 1 Width	645 mm
Product Name	Frequency Converter
Product Net Depth / Length	506 mm
Product Net Height	1741 mm
Product Net Weight	199 kg
Product Net Width	350 mm
Product Type	ACS880__Frequency_converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS880-04-715A-5 PN: 500KW, IN: 715A
Stocked At (Warehouses)	Zhengzhou, China

	Beijing, China
	Singapore, Singapore
	Beijing, China
	Singapore, Singapore
	Tokyo, Japan
	Australia, Australia
Two Speed Motor	No
UNSPSC	39122001
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
EPLAN Data Portal Status	Available but Not EDS Compliant