



PRODUCT-DETAILS

ACS880-04-330A-7

ACS880-04-330A-7 PN: 315KW, IN: 330A

General Information

Global Commercial Alias	ACS880-04-330A-7
Product ID	3ABD0000151831
ABB Type Designation	ACS880-04-330A-7
Catalog Description	ACS880-04-330A-7 PN: 315KW, IN: 330A
Long Description	ACS880-04-330A-7

Additional Information

ABB Type Designation	ACS880-04-330A-7
CN8	85044084
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R10
Global Commercial Alias	ACS880-04-330A-7
Gross Volume	31 dm ³
Gross Weight	212.5 kg
Invoice Description	ACS880-04-330A-7 PN: 315KW, IN: 330A
IP Class	IP21
Made To Order	No
Medium Description	ACS880-04-330A-7 PN: 315KW, IN: 330A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	2050 mm
Package Level 1 Gross Weight	212.5 kg
Package Level 1 Height	690 mm
Package Level 1 Units	1 carton
Package Level 1 Width	645 mm
Product Name	Frequency Converter
Product Net Depth / Length	506 mm
Product Net Height	1541 mm
Product Net Weight	161 kg
Product Net Width	350 mm
Product Type	ACS880_Frequency_converter

Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS880-04-330A-7 PN: 315KW, IN: 330A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
Two Speed Motor	No
UNSPSC	39122001
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
EPLAN Data Portal Status	Available and EDS Compliant