



PRODUCT-DETAILS

# ACS880-04-880A-5

ACS880-04-880A-5 PN: 630KW, IN: 880A

## General Information

Global Commercial Alias	ACS880-04-880A-5
Product ID	3ABD0000169453
ABB Type Designation	ACS880-04-880A-5
Catalog Description	ACS880-04-880A-5 PN: 630KW, IN: 880A
Long Description	ACS880-04-880A-5

## Additional Information

ABB Type Designation	ACS880-04-880A-5
CN8	85044090
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R11
Global Commercial Alias	ACS880-04-880A-5
Gross Weight	264 kg
Invoice Description	ACS880-04-880A-5 PN: 630KW, IN: 880A
IP Class	IP21
Made To Order	No
Medium Description	ACS880-04-880A-5 PN: 630KW, IN: 880A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	2050 mm
Package Level 1 Gross Weight	264 kg
Package Level 1 Height	690 mm
Package Level 1 Units	1 carton
Package Level 1 Width	645 mm
Product Name	Frequency Converter
Product Net Depth / Length	506 mm
Product Net Height	1741 mm
Product Net Weight	199 kg
Product Net Width	350 mm
Product Type	ACS880_Frequency_converter
Quote Only	No

Selling Unit of Measure	piece
Short Description	ACS880-04-880A-5 PN: 630KW, IN: 880A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
Two Speed Motor	No
UNSPSC	39122001
WEEE B2C / B2B	Business To Business
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)