

PRODUCT-DETAILS

ACS880-01-032A-3+E200

ACS880-01-032A-3+E200 PN: 15KW, IN: 32A



General Information	
Global Commercial Alias	ACS880-01-032A-3+E200
Product ID	3ABD00038082-D
ABB Type Designation	ACS880-01-032A-3+E200
Catalog Description	ACS880-01-032A-3+E200 PN: 15KW, IN: 32A
Long Description	<p>The ACS880-01 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps, and fans. The ACS880-01 comes in one compact package for easy installation and commissioning. The drive can be installed on the wall as standard and in a cabinet as an option. The drive offering includes enclosure classes up to IP55, making it suitable for most environments and installations. ACS880-01 drives have all the essential features built-in. These features include as standard a choke for harmonic filtering as well as options like a brake chopper, EMC filter and communication protocol adapter, functional safety, external output filters, and I/O extension modules.</p>

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099

Invoice Description	ACS880-01-032A-3+E200 PN: 15KW, IN: 32A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information

Gross Volume	31 dm³
--------------	--------

Dimensions

Product Net Weight	10 kg
Product Net Depth / Length	261 mm
Product Net Height	475 mm
Product Net Width	172 mm
Package Level 1 Depth / Length	620 mm
Package Level 1 Height	320 mm
Package Level 1 Width	250 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R3
Input Voltage (U _{in})	380 ... 415 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I _{HD})	25 A
Output Current, Light-Overload Use (I _{LD})	30 A
Output Current, Normal Use (I _n)	32 A
Output Power, Heavy-Duty Use (P _{HD})	11 kW
Output Power, Light-Overload Use (P _{LD})	15 kW
Output Power, Normal	15 kW

Use (P_n)

Efficiency Level	IE2
------------------	-----

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)
---------------	---

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-01 - Wall-mounted single drive

