



PRODUCT-DETAILS

3ABD00046021

ACS355 English Manual

General Information

Product ID	3ABD00046021
ABB Type Designation	ACS355 English Manual
Catalog Description	ACS355 English Manual
Long Description	The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications. The drive are user-friendly, yet provide a wide range of built-in technology, such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.

Additional Information

ABB Type Designation	ACS355 English Manual
CN8	85044081
Country of Origin	China (CN)
Customs Tariff Number	85044081
Frame Size	R1
Gross Weight	2 kg
Invoice Description	ACS355 English Manual
Made To Order	No
Minimum Order Quantity	1 piece
Module Function	LV AC machinery drive module
Order Multiple	1 piece
Package Level 1 Units	0 carton
Product Name	FREQUENCY CONVERTER
Product Net Depth / Length	342 mm
Product Net Height	130 mm
Product Net Weight	0 kg
Product Net Width	215 mm
Product Type	ACS355_Frequency_Converter
Quote Only	No
Replaced Product ID (OLD)	3ABD68496977 3ABD68866162
Selling Unit of Measure	piece
Short Description	ACS355 English Manual
Stocked At (Warehouses)	Zhengzhou, China Singapore, Singapore Beijing, China Singapore, Singapore

	Tokyo, Japan
	Australia, Australia
Two Speed Motor	No
UNSPSC	39122001
WEEE Category	Product Not in WEEE Scope