



PRODUCT-DETAILS

ACS150-01E-02A4-2+N7522

ACS150-01E-02A4-2+N7522 PN:0.37KW 2.4A

General Information

Global Commercial Alias	ACS150-01E-02A4-2+N7522
Product ID	3ABD00046470
ABB Type Designation	ACS150-01E-02A4-2+N7522
Catalog Description	ACS150-01E-02A4-2+N7522 PN:0.37KW 2.4A

Long Description

The ACS150 drives are designed to be incorporated into a wide variety of machines such as mixers, conveyors, fans or pumps. The ACS150 drives have an integrated user panel, potentiometer, and a variety of features, such as pre-defined connection macros, making drive selection and configuration easy. With an optional FlashDrop tool, these drives can be configured quickly in volume.

Additional Information

ABB EcoSolutions	Yes
ABB Type Designation	ACS150-01E-02A4-2+N7522
Circular Design Principles Lifetime	3AXD10001912952
Circular Design Principles Recyclability Rate	90 %
CN8	85044096
Country of Origin	China (CN)
Customs Tariff Number	85044099
End of Life Instructions	3AXD50000153893
Environmental Product Declaration - EPD	3AXD10001912952
Frame Size	R0
Global Commercial Alias	ACS150-01E-02A4-2+N7522
Gross Weight	2 kg
Improved Resource Efficiency for Customers	Product Efficiency - Product considered more energy-efficient compared to similar product on market or older products from the same line Process Efficiency - Product contribute to making customer's operations more resilient and reliable Digital Efficiency - Product is digitally-supported to optimize usage and eventually optimize customer asset

Invoice Description	ACS150-01E-02A4-2+N7522 PN:0.37KW 2.4A
Made To Order	No
Medium Description	ACS150-01E-02A4-2+N7522 PN:0.37KW 2.4A
Minimum Order Quantity	1 piece
Module Function	LV AC micro drive
Offered with Extended Lifetime	Lifetime extension of customer's assets is made possible thanks to offering and the supporting services
Order Multiple	1 piece
Package Level 1 Depth / Length	350 mm
Package Level 1 Gross Weight	2 kg
Package Level 1 Height	130 mm
Package Level 1 Units	0 carton
Package Level 1 Width	220 mm
Product Name	frequency converter
Product Net Depth / Length	342 mm
Product Net Height	130 mm
Product Net Weight	0 kg
Product Net Width	215 mm
Product Type	ACS150_Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS150-01E-02A4-2+N7522 PN:0.37KW 2.4A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
Sustainable Material Content	Recycled Metal - 34 %
Sustainable Material Content in Packaging	90 %
UNSPSC	39122001
WEEE B2C / B2B	Business To Business
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)