

PRODUCT-DETAILS

ACS355-03E-12A5-4+N2002

ACS355-03E-12A5-4 +N2002 PN:5.5KW 12.5A



General Information

Global Commercial Alias	ACS355-03E-12A5-4+N2002
Product ID	3ABD00046617
ABB Type Designation	ACS355-03E-12A5-4+N2002
Catalog Description	ACS355-03E-12A5-4 +N2002 PN:5.5KW 12.5A
Long Description	The ACS355 drives are designed to meet the requirements of an extensive range of machinery applications in food and beverage, material handling, lifting, textile, printing, rubber and plastics, and woodworking applications. The drive are user-friendly, yet provide a wide range of built-in technology, such as the safe torque off functionality and sequence programming, reducing the need for additional control electronics. The product offers options and diverse functionality to cater to the needs set for speed and torque control of AC induction and permanent magnet motors.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS355-03E-12A5-4 +N2002 PN:5.5KW 12.5A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	0 kg
Product Net Depth / Length	342 mm
Product Net Height	130 mm
Product Net Width	215 mm
Package Level 1 Depth / Length	330 mm
Package Level 1 Height	220 mm
Package Level 1 Width	205 mm
Package Level 1 Units	0 carton

Technical	
Frame Size	R3
Efficiency Level	IE2

Additional Information	
Product Name	FREQUENCY CONVERTER

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → Machinery Drives → ACS355 - Machinery Drive	

