

## PRODUCT-DETAILS

# ACS580-04-585A-4+H356+N7511, Saidel

## LV AC general purpose drive module (ACS580-04-585A-4+H356+N7511, Saidel)



### General Information

|                         |   |
|-------------------------|---|
| Global Commercial Alias | ACS580-04-585A-4+H356+N7511, Saidel   |
| Product ID              | 3ABD00047079-D  |
| ABB Type Designation    | ACS580-04-585A-4+H356+N7511, Saidel   |
| Catalog Description     | LV AC general purpose drive module (ACS580-04-585A-4+H356+N7511, Saidel)  |
| Long Description        | <p>The ACS580-04 is plug-in ready to control your compressors, conveyors, pumps, extruders, centrifuges, mixers, fans, and many other variable and constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. A versatile and straightforward settings menu and assistants enable fast setup, commissioning, use, and maintenance, while a rugged and robust design makes it a good fit for various environments. With the ACS580 drives, you can easily take full control of your processes to comprehensively manage your plant. The ACS580-04 drive module comes in an IP00 enclosure as standard for cabinet installation. In addition, an IP20 enclosure is available.</p> |

### Ordering

|                        |   |
|------------------------|---|
| Country of Origin      | China (CN)  |
| Customs Tariff Number  | 85044099  |
| Invoice Description    | ACS580-04-585A-4+H356+N7511, Saideli customization PN:315kW, IN: 585A |
| Made To Order          | No  |
| Minimum Order Quantity | 1 piece   |

|                         |       |
|-------------------------|-------|
| Quote Only              | No    |
| Selling Unit of Measure | piece |

|                       |         |
|-----------------------|---------|
| Container Information |         |
| Gross Volume          | 161 dm³ |

|                                |          |
|--------------------------------|----------|
| Dimensions                     |          |
| Product Net Weight             | 161 kg   |
| Product Net Depth / Length     | 529 mm   |
| Product Net Height             | 1462 mm  |
| Product Net Width              | 345 mm   |
| Package Level 1 Depth / Length | 1000 mm  |
| Package Level 1 Height         | 500 mm   |
| Package Level 1 Width          | 400 mm   |
| Package Level 1 Units          | 0 carton |

|                  |     |
|------------------|-----|
| Technical        |     |
| Frame Size       | R10 |
| Efficiency Level | IE2 |

|                        |                     |
|------------------------|---------------------|
| Additional Information |                     |
| Product Name           | Frequency Converter |

|                 |          |
|-----------------|----------|
| Classifications |          |
| UNSPSC          | 39122001 |

|               |                           |
|---------------|---------------------------|
| Environmental |                           |
| WEEE Category | Product Not in WEEE Scope |

|            |  |
|------------|--|
| Categories |  |
|------------|--|

Drives → Low Voltage AC Drives → General Purpose Drives → ACS580-04 - Drive module

