

## PRODUCT-DETAILS

# ACS880-01-293A-3+N5700

## ACS880 N5700 position drive, 400 VAC, PN: 160 kW, IN: 293 A



### General Information

Global Commercial Alias	ACS880-01-293A-3+N5700
Product ID	3ABD00048191-D
ABB Type Designation	ACS880-01-293A-3+N5700
Catalog Description	ACS880 N5700 position drive, 400 VAC, PN: 160 kW, IN: 293 A
Long Description	The ACS880 drives which are configured with the position control program (+N5700) is an ideal choice for high-power position control axes. Its motion functions are based on PLCopen motion control blocks and can be easily configured by parameters. Programming flexibility and connectivity to all motors and PLCs ensure optimized solutions for production machinery and material handling applications.

### Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS880 N5700 position drive, 400 VAC, PN: 160 kW, IN: 293 A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	68 kg
Product Net Depth / Length	386 mm
Product Net Height	963 mm
Product Net Width	300 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	48 ... 63 Hz
Frame Size	R8
Input Voltage ( $U_{in}$ )	380 ... 415 V
Mounting Type	Wall-mounted
Output Current, Heavy-Duty Use ( $I_{HD}$ )	246 A
Output Current, Light-Overload Use ( $I_{LD}$ )	278 A
Output Current, Normal Use ( $I_n$ )	293 A
Output Power, Heavy-Duty Use ( $P_{HD}$ )	132 kW
Output Power, Light-Overload Use ( $P_{LD}$ )	160 kW
Output Power, Normal Use ( $P_n$ )	160 kW

Additional Information	
Product Name	ACS880-01 + N5700

Classifications	
UNSPSC	39122003

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

---

## Categories

---

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-01 - Wall-mounted single drive

