

PRODUCT-DETAILS

# ACS530-01-062A-4+N7562

ACS530-01-062A-4+N7562 PN: 30kW, IN: 62A



## General Information

Global Commercial Alias	ACS530-01-062A-4+N7562
Product ID	3ABD00049208-D
ABB Type Designation	ACS530-01-062A-4+N7562
Catalog Description	ACS530-01-062A-4+N7562 PN: 30kW, IN: 62A
Long Description	The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.

## Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044086
Invoice Description	ACS530-01-062A-4+N7562 PN: 30kW, IN: 62A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

Dimensions	
Product Net Weight	18.5 kg
Product Net Depth / Length	257 mm
Product Net Height	636 mm
Product Net Width	203 mm
Package Level 1 Depth / Length	720 mm
Package Level 1 Height	380 mm
Package Level 1 Width	300 mm
Package Level 1 Units	1 carton

Technical	
Frame Size	R4
Efficiency Level	IE2

Additional Information	
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive	

