



PRODUCT-DETAILS

HDS130-1225AMKBN

HDS series motor, 230 VAC, flange size 130 mm, low inerita, 2.5 kW, 17-bit multi-turn SmartABS, key, brake, no seal

General Information	
Global Commercial Alias	HDS130-1225AMKBN
Product ID	3ABD00049354
ABB Type Designation	HDS130-1225AMKBN
Catalog Description	HDS series motor, 230 VAC, flange size 130 mm, low inerita, 2.5 kW, 17-bit multi-turn SmartABS, key, brake, no seal

Additional Information	
ABB Type Designation	HDS130-1225AMKBN
CN8	85044088
Country of Origin	Finland (FI)
Customs Tariff Number	8501520000
Frame Size	A
Global Commercial Alias	HDS130-1225AMKBN
Gross Weight	11.35 kg
Invoice Description	HDS series motor, 230 VAC, flange size 130 mm, low inerita, 2.5 kW, 17-bit multi-turn SmartABS, key, brake, no seal
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	380 mm
Package Level 1 Height	231 mm
Package Level 1 Units	1 carton
Package Level 1 Width	190 mm
Product Name	HDS Motor
Product Net Depth / Length	283 mm
Product Net Height	170 mm
Product Net Weight	10.7 kg
Product Net Width	130 mm
Product Type	HDS_servo_motor
Quote Only	No
Replaced Product ID (OLD)	3ABD00024309
Selling Unit of Measure	piece

Short Description	HDS series motor, 230 VAC, flange size 130 mm, low inerita, 2.5 kW, 17-bit multi-turn SmartABS, key, brake, no seal
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Shanghai, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
Two Speed Motor	No
UNSPSC	26101109
WEEE B2C / B2B	Business To Business
WEEE Category	Product Not in WEEE Scope