

PRODUCT-DETAILS

HDS180C-3555BSKBS

HDS series motor, 400 VAC, flange size 180 mm, high inerita, 5.5 kW, 17-bit single-turn SmartABS, key, brake, seal



General Information	
Global Commercial Alias	HDS180C-3555BSKBS
Product ID	3ABD00049789
ABB Type Designation	HDS180C-3555BSKBS
Catalog Description	HDS series motor, 400 VAC, flange size 180 mm, high inerita, 5.5 kW, 17-bit single-turn SmartABS, key, brake, seal
Long Description	The HDS series servo motors provide more effective combinations of torque and inertia. Equipped with various high performance and high-resolution feedback options, HDS meets various requirements of applications and drives. By providing control on speed, torque and position with high precision and quality for the operation of terminal equipment, HDS helps to improve the efficiency and stability of the equipment and ensure higher reliability of the complete system.

Additional Information	
ABB Type Designation	HDS180C-3555BSKBS
CN8	85044088
Country of Origin	China (CN)
Customs Tariff Number	8501520000
Degree of Protection	IP65
Flange Size Range	180 mm
Frame Size	A
Global Commercial Alias	HDS180C-3555BSKBS

Gross Weight	35.3 kg
Input Voltage (U _{in})	400 V
Invoice Description	HDS series motor, 400 VAC, flange size 180 mm, high inertia, 5.5 kW, 17-bit single-turn SmartABS, key, brake, seal
Made To Order	No
Maximum Peak Current	68.5 A
Maximum Peak Torque	105 N·m
Maximum Speed	3500 r/min
Minimum Order Quantity	1 piece
Motor Power AC-3	5.5 kW
Number of Phases	3
Order Multiple	1 piece
Package Level 1 Depth / Length	520 mm
Package Level 1 Height	302 mm
Package Level 1 Units	1 carton
Package Level 1 Width	265 mm
Product Name	HDS motor
Product Net Depth / Length	406 mm
Product Net Height	240 mm
Product Net Weight	33.9 kg
Product Net Width	180 mm
Product Type	HDS_servo_motor
Quote Only	No
Rated Output Current	22.3 A
Rated Speed	1500 r/min
Rated Torque	35 N·m
Replaced Product ID (OLD)	3ABD00024309
Selling Unit of Measure	piece
Shaft Diameter	35 mm
Shaft Length	80 mm
Short Description	HDS series motor, 400 VAC, flange size 180 mm, high inertia, 5.5 kW, 17-bit single-turn SmartABS, key, brake, seal
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Shanghai, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
Two Speed Motor	No
UNSPSC	26101109
WEEE B2C / B2B	Business To Business
WEEE Category	Product Not in WEEE Scope

Categories

Motors and Generators → Servomotors → AC Brushless Servo Motors → AC Brushless HDS Series Motors

