

PRODUCT-DETAILS

ACS530-01-062A-4+P973

ACS530-01-062A-4+P973 PN:30kW, IN:62A



General Information	
Global Commercial Alias	ACS530-01-062A-4+P973
Product ID	3ABD00049999-D
ABB Type Designation	ACS530-01-062A-4+P973
Catalog Description	ACS530-01-062A-4+P973 PN:30kW, IN:62A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments.</p> <p>The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-062A-4+P973 PN:30kW, IN:62A
Made To Order	No
Minimum Order Quantity	1 piece

Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	18.5 kg
Product Net Depth / Length	257 mm
Product Net Height	636 mm
Product Net Width	203 mm
Package Level 1 Depth / Length	720 mm
Package Level 1 Height	380 mm
Package Level 1 Width	300 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R4
Input Voltage (U_{in})	380 ... 500 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Light-Overload Use (I_{LD})	58 A
Output Current, Normal Use (I_n)	62 A
Output Power, Light-Overload Use (P_{LD})	30 kW
Output Power, Normal Use (P_n)	30 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	241 W	0.6 %	90.4 %
0 / 50 %	316 W	0.7 %	93.3 %
0 / 100 %	569 W	1.3 %	93.9 %
50 / 25 %	264 W	0.6 %	94.7 %
50 / 50 %	364 W	0.8 %	96.2 %
50 / 100 %	677 W	1.6 %	96.4 %
90 / 50 %	424 W	1 %	97.5 %
90 / 100 %	867 W	2 %	97.4 %

Additional Information

Product NameFrequency Converter

Classifications

UNSPSC39122001

Environmental

WEEE Category5. Small Equipment (No External Dimension More Than 50 cm)

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive

