

PRODUCT-DETAILS

ACS530-01-018A-4+N7569

ACS530-01-018A-4+N7569 PN: 7.5kW, IN: 17A



General Information

Global Commercial Alias	ACS530-01-018A-4+N7569
Product ID	3ABD00050258-D
ABB Type Designation	ACS530-01-018A-4+N7569
Catalog Description	ACS530-01-018A-4+N7569 PN: 7.5kW, IN: 17A
Long Description	The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS530-01-018A-4+N7569 PN: 7.5kW, IN: 17A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

Dimensions

Product Net Weight	6 kg
Product Net Depth / Length	229 mm
Product Net Height	432 mm
Product Net Width	125 mm
Package Level 1 Depth / Length	425 mm
Package Level 1 Height	620 mm
Package Level 1 Width	225 mm
Package Level 1 Units	1 carton

Technical

Frame Size	R2
Efficiency Level	IE2

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive

