

PRODUCT-DETAILS

ACS530-01-293A-4+N7569

ACS530-01-293A-4+N7569 PN: 160kW, IN: 293A



General Information

Global Commercial Alias	ACS530-01-293A-4+N7569
Product ID	3ABD00050271-D
ABB Type Designation	ACS530-01-293A-4+N7569
Catalog Description	ACS530-01-293A-4+N7569 PN: 160kW, IN: 293A
Long Description	<p>The ACS530-01 can control your compressors, conveyors, pumps, centrifuges, fans, and many other variable and simple constant torque applications, in a variety of light industries, including food and beverage, plastic, textile, material handling, and agriculture. All essential features are built-in as standard, simplifying drive selection, and making additional hardware unnecessary. The basic control panel enable fast setup, commissioning, use, and maintenance, while a rugged and robust design make it a good fit for various environments. The wall-mounted ACS530-01 comes in an IP20 enclosure as standard.</p>

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-01-293A-4+N7569 PN: 160kW, IN: 293A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No

Selling Unit of Measure

piece

Dimensions	
Product Net Weight	62.8 kg
Product Net Depth / Length	393 mm
Product Net Height	680 mm
Product Net Width	300 mm
Package Level 1 Depth / Length	1160 mm
Package Level 1 Height	650 mm
Package Level 1 Width	490 mm
Package Level 1 Units	1 carton

Technical	
Frame Size	R8
Efficiency Level	IE2

Additional Information	
Product Name	Frequency Converter

Classifications	
UNSPSC	39122001

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories	
Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-01 - Wall-mounted drive	

