

PRODUCT-DETAILS

ACS530-04-880A-4+N7569+B051

ACS530-04-880A-4+N7569+B051 PN: 500kW, IN: 880A



General Information

Global Commercial Alias	ACS530-04-880A-4+N7569+B051
Product ID	3ABD00050294-D
ABB Type Designation	ACS530-04-880A-4+N7569+B051
Catalog Description	ACS530-04-880A-4+N7569+B051 PN: 500kW, IN: 880A
Long Description	ACS530-04-880A-4+N7569+B051

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS530-04-880A-4+N7569+B051 PN: 500kW, IN: 880A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	199 kg
Product Net Depth / Length	529 mm

Product Net Height	1662 mm
Product Net Width	350 mm
Package Level 1 Depth / Length	2050 mm
Package Level 1 Height	500 mm
Package Level 1 Width	645 mm
Package Level 1 Units	1 carton

Technical

Frame Size	R11
Efficiency Level	IE2

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → General Purpose Drives → ACS530-04 - Drive module

