



PRODUCT-DETAILS

ACS530-01-02A7-4+N7569+P974

ACS530-01-02A7-4+N7569+P974 PN: 0.75kW, IN: 2.6A

General Information

| | |
|-------------------------|--|
| Global Commercial Alias | ACS530-01-02A7-4+N7569+P974 |
| Product ID | 3ABD00058110-D |
| ABB Type Designation | ACS530-01-02A7-4+N7569+P974 |
| Catalog Description | ACS530-01-02A7-4+N7569+P974 PN: 0.75kW, IN: 2.6A |

Additional Information

| | |
|--|---|
| ABB EcoSolutions | Yes |
| ABB Type Designation | ACS530-01-02A7-4+N7569+P974 |
| Circular Design Principles Lifetime | 3AXD10001912952 |
| Circular Design Principles Recyclability Rate | 90 % |
| Country of Origin | China (CN) |
| Customs Tariff Number | 85044099 |
| End of Life Instructions | 3AXD50000153893 |
| Environmental Product Declaration - EPD | 3AXD10001912952 |
| Frame Size | R1 |
| Global Commercial Alias | ACS530-01-02A7-4+N7569+P974 |
| Gross Weight | 6.5 kg |
| Improved Resource Efficiency for Customers | Product Efficiency - Product considered more energy-efficient compared to similar product on market or older products from the same line Process Efficiency - Product contribute to making customer's operations more resilient and reliable Digital Efficiency - Product is digitally-supported to optimize usage and eventually optimize customer asset |
| Invoice Description | ACS530-01-02A7-4+N7569+P974 PN: 0.75kW, IN: 2.6A |
| Made To Order | No |
| Medium Description | ACS530-01-02A7-4+N7569+P974 PN: 0.75kW, IN: 2.6A |
| Minimum Order Quantity | 1 piece |
| Offered with Extended | Lifetime extension of customer's assets is made possible thanks to offering and |

| | |
|---|---|
| Lifetime | the supporting services |
| Order Multiple | 1 piece |
| Package Level 1 Depth / Length | 525 mm |
| Package Level 1 Gross Weight | 6.5 kg |
| Package Level 1 Height | 425 mm |
| Package Level 1 Units | 1 carton |
| Package Level 1 Width | 225 mm |
| Product Name | Frequency Converter |
| Product Net Depth / Length | 223 mm |
| Product Net Height | 331 mm |
| Product Net Weight | 4 kg |
| Product Net Width | 125 mm |
| Product Type | ACS530_Frequency_converter |
| Quote Only | No |
| Selling Unit of Measure | piece |
| Short Description | ACS530-01-02A7-4+N7569+P974 PN: 0.75kW, IN: 2.6A |
| Stocked At (Warehouses) | Zhengzhou, China Beijing, China Shanghai, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia |
| Sustainable Material Content | Recycled Metal - 34 % |
| Sustainable Material Content in Packaging | 90 % |
| Two Speed Motor | No |
| UNSPSC | 39122001 |