



PRODUCT-DETAILS

# ACS380-040C-12A6-4+L538+N7588

ACS380-040C-12A6-4+L538+N7588 PN: 5.5kW,  
IN: 12.6A

## General Information

Global Commercial Alias	ACS380-040C-12A6-4+L538+N7588
Product ID	3ABD00058734
ABB Type Designation	ACS380-040C-12A6-4+L538+N7588
Catalog Description	ACS380-040C-12A6-4+L538+N7588 PN: 5.5kW, IN: 12.6A

## Additional Information

ABB Type Designation	ACS380-040C-12A6-4+L538+N7588
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R2
Global Commercial Alias	ACS380-040C-12A6-4+L538+N7588
Gross Weight	2 kg
Invoice Description	ACS380-040C-12A6-4+L538+N7588 PN: 5.5kW, IN: 12.6A
Made To Order	No
Maximum Order Quantity	10 piece
Medium Description	ACS380-040C-12A6-4+L538+N7588 PN: 5.5kW, IN: 12.6A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	280 mm
Package Level 1 Gross Weight	2 kg
Package Level 1 Height	270 mm
Package Level 1 Units	0 carton
Package Level 1 Width	145 mm
Product Name	FREQUENCY CONVERTER
Product Net Depth / Length	176 mm
Product Net Height	223 mm
Product Net Weight	1.4 kg
Product Net Width	70 mm
Product Type	ACS380__Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece

Short Description	ACS380-040C-12A6-4+L538+N7588 PN: 5.5kW, IN: 12.6A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Shanghai, China Singapore, Singapore Beijing, China Singapore, Singapore Tokyo, Japan Australia, Australia
UNSPSC	39122001