

PRODUCT-DETAILS

ACS880-04-505A-3+H356+N5700

, IEC: Pn 250 kW, 505 A (ACS880-04-505A-3+H356+N5700)



General Information

Global Commercial Alias	ACS880-04-505A-3+H356+N5700
Product ID	3ABD00058756-D
ABB Type Designation	ACS880-04-505A-3+H356+N5700
Catalog Description	, IEC: Pn 250 kW, 505 A (ACS880-04-505A-3+H356+N5700)
Long Description	The ACS880 drives which are configured with the position control program (+N5700) is an ideal choice for high-power position control axes. Its motion functions are based on PLCopen motion control blocks and can be easily configured by parameters. Programming flexibility and connectivity to all motors and PLCs ensure optimized solutions for production machinery and material handling applications.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS880 N5700 position drive, 400 VAC, PN: 250 kW, IN: 505 A, DC connection bus bars/terminals
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Container Information	
Gross Volume	30 dm³

Dimensions	
Product Net Weight	161 kg
Product Net Depth / Length	506 mm
Product Net Height	1541 mm
Product Net Width	350 mm
Package Level 1 Depth / Length	690 mm
Package Level 1 Height	2050 mm
Package Level 1 Width	645 mm
Package Level 1 Units	1 carton

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	48 ... 63 Hz
Frame Size	R10
Input Voltage (U_{in})	380 ... 415 V
Mounting Type	Module
Output Current, Heavy-Duty Use (I_{HD})	361 A
Output Current, Light-Overload Use (I_{LD})	485 A
Output Current, Normal Use (I_n)	505 A
Output Power, Heavy-Duty Use (P_{HD})	200 kW
Output Power, Light-Overload Use (P_{LD})	250 kW
Output Power, Normal Use (P_n)	250 kW

Additional Information	
Product Name	ACS880-04 + N5700

Classifications	
UNSPSC	39122001

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 drive modules → ACS880-04 - Single drive module

