

PRODUCT-DETAILS

ACS880-01-430A-3+D150+B056+N5700

ACS880 N5700 position drive, 400 VAC, PN: 250 kW, IN: 430 A, brake chopper, IP55



General Information

Global Commercial Alias	ACS880-01-430A-3+D150+B056+N5700
Product ID	3ABD00058859-D
ABB Type Designation	ACS880-01-430A-3+D150+B056+N5700
Catalog Description	ACS880 N5700 position drive, 400 VAC, PN: 250 kW, IN: 430 A, brake chopper, IP55
Long Description	The ACS880 drives which are configured with the position control program (+N5700) is an ideal choice for high-power position control axes. Its motion functions are based on PLCopen motion control blocks and can be easily configured by parameters. Programming flexibility and connectivity to all motors and PLCs ensure optimized solutions for production machinery and material handling applications.

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044085
Invoice Description	ACS880 N5700 position drive, 400 VAC, PN: 250 kW, IN: 430 A, brake chopper, IP55
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	0 kg
Product Net Depth / Length	477 mm
Product Net Height	955 mm
Product Net Width	380 mm
Package Level 1 Depth / Length	650 mm
Package Level 1 Height	1160 mm
Package Level 1 Width	490 mm
Package Level 1 Units	1 carton

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Open Type
Frequency (f)	48 ... 63 Hz
Frame Size	R9
Input Voltage (U_{in})	380 ... 415 V
Mounting Type	Wall-mounted
Output Current, Heavy-Duty Use (I_{HD})	363 A
Output Current, Light-Overload Use (I_{LD})	400 A
Output Current, Normal Use (I_n)	430 A
Output Power, Heavy-Duty Use (P_{HD})	200 kW
Output Power, Light-Overload Use (P_{LD})	200 kW
Output Power, Normal Use (P_n)	200 kW

Additional Information

Product Name	ACS880-01 + N5700
--------------	-------------------

Classifications

UNSPSC	39122001
--------	----------

Categories

Drives → Low Voltage AC Drives → Industrial Drives → ACS880 single drives → ACS880-01 - Wall-mounted single drive

