



PRODUCT-DETAILS

HXA102025AR0NK0

HX series motor, 230 VAC, T4, flange size 100 mm, 2.02 kW, resolver, no brake



General Information

Global Commercial Alias	HXA102025AR0NK0
Product ID	3ABD00058981
ABB Type Designation	HXA102025AR0NK0
Catalog Description	HX series motor, 230 VAC, T4, flange size 100 mm, 2.02 kW, resolver, no brake
Long Description	HX 102025AR0NK0 102025AR0NK0 102025AR0NK0CCC Ex db IIC T5/T4 Gb Ex tb IICT100/T130 Db IP66

Additional Information

ABB Type Designation	HXA102025AR0NK0
Country of Origin	China (CN)
Customs Tariff Number	8501520000
Degree of Protection	IP65
Flange Size Range	100 mm
Global Commercial Alias	HXA102025AR0NK0
Gross Weight	6.66 kg
Input Voltage (U <sub>in</sub> )	230 V
Invoice Description	HX series motor, 230 VAC, T4, flange size 100 mm, 2.02 kW, resolver, no brake

Made To Order	No
Maximum Peak Current	36.9 A
Maximum Peak Torque	23.6 N·m
Minimum Order Quantity	1 piece
Motor Power AC-3	2.02 kW
Number of Phases	3
Order Multiple	1 piece
Package Level 1 Depth / Length	380 mm
Package Level 1 Height	231 mm
Package Level 1 Units	0 carton
Package Level 1 Width	190 mm
Product Name	HX motor
Product Net Depth / Length	304 mm
Product Net Height	134 mm
Product Net Weight	5.97 kg
Product Net Width	100 mm
Product Type	Undefined
Quote Only	No
Rated Output Current	9.2 A
Rated Speed	2500 r/min
Rated Torque	7.7 N·m
Selling Unit of Measure	piece
Shaft Diameter	19 mm
Shaft Length	40 mm
Short Description	HX series motor, 230 VAC, T4, flange size 100 mm, 2.02 kW, resolver, no brake
Stocked At (Warehouses)	Beijing, China Beijing, China

Categories

Motors and Generators → Servomotors → AC Brushless Servo Motors → AC Brushless HDS Series Motors

