

Made To Order	No
Maximum Peak Current	12 A
Maximum Peak Torque	7 N·m
Minimum Order Quantity	1 piece
Motor Power AC-3	0.85 kW
Number of Phases	3
Order Multiple	1 piece
Package Level 1 Depth / Length	360 mm
Package Level 1 Height	187 mm
Package Level 1 Units	0 carton
Package Level 1 Width	165 mm
Product Name	HX motor
Product Net Depth / Length	251 mm
Product Net Height	103 mm
Product Net Weight	2.84 kg
Product Net Width	70 mm
Product Type	Undefined
Quote Only	No
Rated Output Current	3.9 A
Rated Speed	3000 r/min
Rated Torque	2.72 N·m
Selling Unit of Measure	piece
Shaft Diameter	11 mm
Shaft Length	23 mm
Short Description	HX series motor, 230 VAC, T4, flange size 70 mm, 0.85 kW, hipurface, no brake
Stocked At (Warehouses)	Beijing, China Beijing, China

Categories

Motors and Generators → Servomotors → AC Brushless Servo Motors → AC Brushless HDS Series Motors

