



PRODUCT-DETAILS

HXA101830AD4NK0

HX series motor, 230 VAC, T4, flange size 100 mm, 1.82 kW, hiperface, no brake



General Information

Global Commercial Alias	HXA101830AD4NK0
Product ID	3ABD00058990
ABB Type Designation	HXA101830AD4NK0
Catalog Description	HX series motor, 230 VAC, T4, flange size 100 mm, 1.82 kW, hiperface, no brake
Long Description	HX CCC Ex db IIC T5/T4 Gb Ex tb IIIC T100 /T130 Db IP66

Additional Information

ABB Type Designation	HXA101830AD4NK0
Country of Origin	China (CN)
Customs Tariff Number	8501520000
Degree of Protection	IP65
Flange Size Range	100 mm
Global Commercial Alias	HXA101830AD4NK0
Gross Weight	5.82 kg
Input Voltage (U _{in})	230 V
Invoice Description	HX series motor, 230 VAC, T4, flange size 100 mm, 1.82 kW, hiperface, no brake

Made To Order	No
Maximum Peak Current	30.5 A
Maximum Peak Torque	17.7 N·m
Minimum Order Quantity	1 piece
Motor Power AC-3	1.82 kW
Number of Phases	3
Order Multiple	1 piece
Package Level 1 Depth / Length	360 mm
Package Level 1 Height	187 mm
Package Level 1 Units	0 carton
Package Level 1 Width	165 mm
Product Name	HX motor
Product Net Depth / Length	282 mm
Product Net Height	134 mm
Product Net Weight	5.36 kg
Product Net Width	100 mm
Product Type	Undefined
Quote Only	No
Rated Output Current	8.2 A
Rated Speed	3000 r/min
Rated Torque	5.8 N·m
Selling Unit of Measure	piece
Shaft Diameter	19 mm
Shaft Length	40 mm
Short Description	HX series motor, 230 VAC, T4, flange size 100 mm, 1.82 kW, hiperface, no brake
Stocked At (Warehouses)	Beijing, China Beijing, China

Categories

Motors and Generators → Servomotors → AC Brushless Servo Motors → AC Brushless HDS Series Motors

