

PRODUCT-DETAILS

HXA704730AR0BK0

HX series motor, 230 VAC, T5, flange size 70 mm, 0.47 kW, resolver, with brake



| General Information | |
|-------------------------|--|
| Global Commercial Alias | HXA704730AR0BK0 |
| Product ID | 3ABD00059075 |
| ABB Type Designation | HXA704730AR0BK0 |
| Catalog Description | HX series motor, 230 VAC, T5, flange size 70 mm, 0.47 kW, resolver, with brake |
| Long Description | HX Series explosion-proof servo motor, with a brand-new explosion-proof design, offers multiple winding types and feedback options. It is designed for Zone 1 explosion-proof environments and adopts an explosion-proof design to ensure the motor casing withstands internal explosions without damage, ensuring equipment safety in gas and dust explosion scenarios. The explosion-proof performance meets the standard, and the CCC explosion-proof certifications are Ex db IIC T5/T4 Gb and Ex tb IIIC T100°C/T130°C Db IP66. |

| Additional Information | |
|-------------------------|-----------------|
| ABB Type Designation | HXA704730AR0BK0 |
| Country of Origin | China (CN) |
| Customs Tariff Number | 8501520000 |
| Degree of Protection | IP65 |
| Flange Size Range | 70 mm |
| Global Commercial Alias | HXA704730AR0BK0 |

| | |
|----------------------------------|--|
| Gross Weight | 3.34 kg |
| Input Voltage (U _{in}) | 230 V |
| Invoice Description | HX series motor, 230 VAC, T5, flange size 70 mm, 0.47 kW, resolver, with brake |
| Made To Order | No |
| Maximum Peak Current | 6 A |
| Maximum Peak Torque | 3.4 N·m |
| Minimum Order Quantity | 1 piece |
| Motor Power AC-3 | 0.47 kW |
| Number of Phases | 3 |
| Order Multiple | 1 piece |
| Package Level 1 Depth / Length | 281 mm |
| Package Level 1 Height | 160 mm |
| Package Level 1 Units | 0 carton |
| Package Level 1 Width | 128 mm |
| Product Name | HX motor |
| Product Net Depth / Length | 233.5 mm |
| Product Net Height | 103 mm |
| Product Net Weight | 2.74 kg |
| Product Net Width | 70 mm |
| Product Type | Undefined |
| Quote Only | No |
| Rated Output Current | 1.9 A |
| Rated Speed | 3000 r/min |
| Rated Torque | 1.5 N·m |
| Selling Unit of Measure | piece |
| Shaft Diameter | 11 mm |
| Shaft Length | 23 mm |
| Short Description | HX series motor, 230 VAC, T5, flange size 70 mm, 0.47 kW, resolver, with brake |
| Stocked At (Warehouses) | Beijing, China Beijing, China |

Categories

Motors and Generators → Servomotors → AC Brushless Servo Motors → AC Brushless HDS Series Motors

