

PRODUCT-DETAILS

3ABD00059671-D
ACS880-01-271A-7+D150+N5700 PN: 250KW,
IN: 271A



General Information	
Global Commercial Alias	3ABD00059671-D
Product ID	3ABD00059671-D
ABB Type Designation	ACS880-01-271A-7+D150+N5700
Catalog Description	ACS880-01-271A-7+D150+N5700 PN: 250KW, IN: 271A
Long Description	<p>The ACS880-01 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps, and fans. The ACS880-01 comes in one compact package for easy installation and commissioning. The drive can be installed on the wall as standard and in a cabinet as an option. The drive offering includes enclosure classes up to IP55, making it suitable for most environments and installations. ACS880-01 drives have all the essential features built-in. These features include as standard a choke for harmonic filtering as well as options like a brake chopper, EMC filter and communication protocol adapter, functional safety, external output filters, and I/O extension modules.</p>

Additional Information	
ABB Type Designation	ACS880-01-271A-7+D150+N5700
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R9

Global Commercial Alias	3ABD00059671-D
Gross Volume	31 dm³
Gross Weight	112 kg
Invoice Description	ACS880-01-271A-7+D150+N5700 PN: 250KW, IN: 271A
IP Class	IP21
Made To Order	No
Medium Description	ACS880-01-271A-7+D150+N5700 PN: 250KW, IN: 271A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	1160 mm
Package Level 1 Gross Weight	112 kg
Package Level 1 Height	650 mm
Package Level 1 Units	1 carton
Package Level 1 Width	490 mm
Product Name	Frequency Converter
Product Net Depth / Length	413 mm
Product Net Height	955 mm
Product Net Weight	98 kg
Product Net Width	380 mm
Product Type	ACS880__Frequency_converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS880-01-271A-7+D150+N5700 PN: 250KW, IN: 271A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Singapore, Singapore Beijing, China Tokyo, Japan Australia, Australia
Two Speed Motor	No
UNSPSC	39122001

