



PRODUCT-DETAILS

ACS380-040C-17A0-4+K457+L515+L535

ACS380-040C-17A0-4+K457+L515+L535 PN: 7.5kW, IN: 17A

General Information

Global Commercial Alias	ACS380-040C-17A0-4+K457+L515+L535
Product ID	3ABD00059692
ABB Type Designation	ACS380-040C-17A0-4+K457+L515+L535
Catalog Description	ACS380-040C-17A0-4+K457+L515+L535 PN: 7.5kW, IN: 17A

Additional Information

ABB Type Designation	ACS380-040C-17A0-4+K457+L515+L535
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R3
Global Commercial Alias	ACS380-040C-17A0-4+K457+L515+L535
Gross Weight	4 kg
Invoice Description	ACS380-040C-17A0-4+K457+L515+L535 PN: 7.5kW, IN: 17A
Made To Order	No
Medium Description	ACS380-040C-17A0-4+K457+L515+L535 PN: 7.5kW, IN: 17A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	280 mm
Package Level 1 Gross Weight	3.5 kg
Package Level 1 Height	270 mm
Package Level 1 Units	0 carton
Package Level 1 Width	245 mm
Product Name	FREQUENCY CONVERTER
Product Net Depth / Length	176 mm
Product Net Height	223 mm
Product Net Weight	3.3 kg
Product Net Width	170 mm
Product Type	ACS380__Frequency_Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS380-040C-17A0-4+K457+L515+L535 PN: 7.5kW, IN: 17A
Stocked At	Zhengzhou, China

(Warehouses)

Beijing, China
Shanghai, China
Singapore, Singapore
Beijing, China
Tokyo, Japan
Australia, Australia

UNSPSC	39122001
--------	----------