



PRODUCT-DETAILS

ACS380-040C-045A-4+K457+L515+L535

ACS380-040C-045A-4+K457+L515+L535 PN:
22kW, IN: 45A

General Information

Global Commercial Alias	ACS380-040C-045A-4+K457+L515+L535
Product ID	3ABD00059697
ABB Type Designation	ACS380-040C-045A-4+K457+L515+L535
Catalog Description	ACS380-040C-045A-4+K457+L515+L535 PN: 22kW, IN: 45A

Additional Information

ABB Type Designation	ACS380-040C-045A-4+K457+L515+L535
Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R4
Global Commercial Alias	ACS380-040C-045A-4+K457+L515+L535
Gross Weight	7 kg
Invoice Description	ACS380-040C-045A-4+K457+L515+L535 PN: 22kW, IN: 45A
Made To Order	No
Medium Description	ACS380-040C-045A-4+K457+L515+L535 PN: 22kW, IN: 45A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	355 mm
Package Level 1 Gross Weight	7 kg
Package Level 1 Height	270 mm
Package Level 1 Units	0 carton
Package Level 1 Width	290 mm
Product Name	FREQUENCY CONVERTER
Product Net Depth / Length	176 mm
Product Net Height	240 mm
Product Net Weight	5.3 kg
Product Net Width	260 mm
Product Type	ACS380 _ Frequency Converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS380-040C-045A-4+K457+L515+L535 PN: 22kW, IN: 45A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Shanghai, China Singapore, Singapore Beijing, China

	Tokyo, Japan
	Australia, Australia
<u>UNSPSC</u>	<u>39122001</u>