

PRODUCT-DETAILS

3ABD00059720-D

ACS880-04-460A-5+D150+E208+N5700 PN:
315KW, IN: 460A



General Information	
Global Commercial Alias	3ABD00059720-D
Product ID	3ABD00059720-D
ABB Type Designation	ACS880-04-460A-5+D150+E208+N5700
Catalog Description	ACS880-04-460A-5+D150+E208+N5700 PN: 315KW, IN: 460A
Long Description	<p>The ACS880-04 drives are customized to meet the particular needs of specific industries, such as oil and gas, mining, metals, chemicals, cement, power plants, material handling, pulp and paper, sawmills, marine, water and wastewater, food and beverage, and automotive. They can control a wide range of applications, including cranes, extruders, winches, winders, conveyors, mixers, compressors, centrifuges, test benches, elevators, extruders, pumps, and fans. The ACS880-04 modules have all the essential features built-in, including a choke for harmonic filtering as standard, and options such as a brake chopper, EMC filter and communication protocol adapter, functional safety and I/O extension modules. The all built-in design combined with IP20 protection significantly simplifies engineering. The drive's compact size, flexible cabling directions and versatile mounting possibilities from narrow bookshelf to flat mounting and horizontal mounting make it an ideal fit for almost any enclosure. The control unit with I/O and communication connections can be mounted outside the power module or integrated into it.</p>

Additional Information	
ABB Type Designation	ACS880-04-460A-5+D150+E208+N5700

Country of Origin	China (CN)
Customs Tariff Number	85044099
Frame Size	R10
Global Commercial Alias	3ABD00059720-D
Gross Volume	31 dm³
Gross Weight	212.5 kg
Invoice Description	ACS880-04-460A-5+D150+E208+N5700 PN: 315KW, IN: 460A
IP Class	IP20
Made To Order	No
Medium Description	ACS880-04-460A-5+D150+E208+N5700 PN: 315KW, IN: 460A
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	2050 mm
Package Level 1 Gross Weight	212.5 kg
Package Level 1 Height	690 mm
Package Level 1 Units	1 carton
Package Level 1 Width	645 mm
Product Name	Frequency Converter
Product Net Depth / Length	506 mm
Product Net Height	1541 mm
Product Net Weight	161 kg
Product Net Width	350 mm
Product Type	ACS880__Frequency_converter
Quote Only	No
Selling Unit of Measure	piece
Short Description	ACS880-04-460A-5+D150+E208+N5700 PN: 315KW, IN: 460A
Stocked At (Warehouses)	Zhengzhou, China Beijing, China Singapore, Singapore Beijing, China Tokyo, Japan Australia, Australia
Two Speed Motor	No
UNSPSC	39122001

