



PRODUCT-DETAILS

HXA186809AR0NK0

HX series motor, 230 VAC, T4, flange size 180 mm, 6.8 kW, resolver, no brake

General Information	
Global Commercial Alias	HXA186809AR0NK0
Product ID	3ABD00059739
ABB Type Designation	HXA186809AR0NK0
Catalog Description	HX series motor, 230 VAC, T4, flange size 180 mm, 6.8 kW, resolver, no brake
Long Description	HX Series explosion-proof servo motor, with a brand-new explosion-proof design, offers multiple winding types and feedback options. It is designed for Zone 1 explosion-proof environments and adopts an explosion-proof design to ensure the motor casing withstands internal explosions without damage, ensuring equipment safety in gas and dust explosion scenarios. The explosion-proof performance meets the standard, and the CCC explosion-proof certifications are Ex db IIC T5/T4 Gb and Ex tb IIIC T100/T130 Db IP66.

Additional Information	
ABB Type Designation	HXA186809AR0NK0
Country of Origin	China (CN)
Customs Tariff Number	8501520000
Global Commercial Alias	HXA186809AR0NK0
Gross Weight	47.5 kg
Invoice Description	HX series motor, 230 VAC, T4, flange size 180 mm, 6.8 kW, resolver, no brake
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	520 mm
Package Level 1 Height	302 mm
Package Level 1 Units	0 carton
Package Level 1 Width	265 mm
Product Name	HX motor
Product Net Weight	46.1 kg
Product Type	Undefined
Quote Only	No
Selling Unit of Measure	piece
Short Description	HX series motor, 230 VAC, T4, flange size 180 mm, 6.8 kW, resolver, no brake
Stocked At (Warehouses)	Beijing, China Beijing, China