



PRODUCT-DETAILS

HXA184111AR0BK0

HX series motor, 230 VAC, T5, flange size 180 mm, 4.19 kW, resolver, with brake

| General Information | |
|-------------------------|--|
| Global Commercial Alias | HXA184111AR0BK0 |
| Product ID | 3ABD00059871 |
| ABB Type Designation | HXA184111AR0BK0 |
| Catalog Description | HX series motor, 230 VAC, T5, flange size 180 mm, 4.19 kW, resolver, with brake |
| Long Description | HX Series explosion-proof servo motor, with a brand-new explosion-proof design, offers multiple winding types and feedback options. It is designed for Zone 1 explosion-proof environments and adopts an explosion-proof design to ensure the motor casing withstands internal explosions without damage, ensuring equipment safety in gas and dust explosion scenarios. The explosion-proof performance meets the standard, and the CCC explosion-proof certifications are Ex db IIC T5/T4 Gb and Ex tb IIIC T100°C/T130°C Db IP66. |

| Additional Information | |
|--------------------------------|---|
| ABB Type Designation | HXA184111AR0BK0 |
| Country of Origin | China (CN) |
| Customs Tariff Number | 8501520000 |
| Global Commercial Alias | HXA184111AR0BK0 |
| Gross Weight | 31.5 kg |
| Invoice Description | HX series motor, 230 VAC, T5, flange size 180 mm, 4.19 kW, resolver, with brake |
| Made To Order | No |
| Minimum Order Quantity | 1 piece |
| Order Multiple | 1 piece |
| Package Level 1 Depth / Length | 520 mm |
| Package Level 1 Height | 302 mm |
| Package Level 1 Units | 0 carton |
| Package Level 1 Width | 265 mm |
| Product Name | HX motor |
| Product Net Weight | 30.1 kg |
| Product Type | Undefined |

| | |
|-------------------------|---|
| Quote Only | No |
| Selling Unit of Measure | piece |
| Short Description | HX series motor, 230 VAC, T5, flange size 180 mm, 4.19 kW, resolver, with brake |
| Stocked At (Warehouses) | Beijing, China Beijing, China |