



PRODUCT-DETAILS

# HXA185820BR0BK0

## HX series motor, 400 VAC, T5, flange size 180 mm, 5.86 kW, resolver, with brake

General Information	
Global Commercial Alias	HXA185820BR0BK0
Product ID	3ABD00059915
ABB Type Designation	HXA185820BR0BK0
Catalog Description	HX series motor, 400 VAC, T5, flange size 180 mm, 5.86 kW, resolver, with brake
Long Description	HX Series explosion-proof servo motor, with a brand-new explosion-proof design, offers multiple winding types and feedback options. It is designed for Zone 1 explosion-proof environments and adopts an explosion-proof design to ensure the motor casing withstands internal explosions without damage, ensuring equipment safety in gas and dust explosion scenarios. The explosion-proof performance meets the standard, and the CCC explosion-proof certifications are Ex db IIC T5/T4 Gb and Ex tb IIIC T100°C/T130°C Db IP66.

Additional Information	
ABB Type Designation	HXA185820BR0BK0
Country of Origin	China (CN)
Customs Tariff Number	8501520000
Global Commercial Alias	HXA185820BR0BK0
Gross Weight	31.5 kg
Invoice Description	HX series motor, 400 VAC, T5, flange size 180 mm, 5.86 kW, resolver, with brake
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Package Level 1 Depth / Length	520 mm
Package Level 1 Height	302 mm
Package Level 1 Units	0 carton
Package Level 1 Width	265 mm
Product Name	HX motor
Product Net Weight	24.2 kg
Product Type	Undefined

Quote Only	No
Selling Unit of Measure	piece
Short Description	HX series motor, 400 VAC, T5, flange size 180 mm, 5.86 kW, resolver, with brake
Stocked At (Warehouses)	Beijing, China Beijing, China