



PRODUCT-DETAILS

ACS150-03E-03A3-4  
ACS150-03E-03A3-4 PN:1.1KW 3.3A



General Information	
Global Commercial Alias	ACS150-03E-03A3-4
Product ID	3ABD68865859
ABB Type Designation	ACS150-03E-03A3-4
Catalog Description	ACS150-03E-03A3-4 PN:1.1KW 3.3A

Ordering	
Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS150-03E-03A3-4 PN:1.1KW 3.3A
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	0 kg
Product Net Depth / Length	142 mm
Product Net Height	169 mm
Product Net Width	70 mm
Package Level 1 Depth / Length	350 mm
Package Level 1 Height	130 mm
Package Level 1 Width	220 mm
Package Level 1 Units	0 carton

Technical	
Number of Phases	3
Degree of Protection	IP20
Enclosure Type NEMA	Open Type
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage ( $U_{in}$ )	380 ... 480 V
Mounting Type	Module_NO UNIT\$
Output Current, Normal Use ( $I_n$ )	3.3 A
Output Power, Normal Use ( $P_n$ )	1.1 kW
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	27 W	1.2 %	81.5 %
0 / 50 %	30 W	1.3 %	88.5 %
0 / 100 %	38 W	1.7 %	91.9 %
50 / 25 %	28 W	1.2 %	89.9 %
50 / 50 %	32 W	1.4 %	93.8 %
50 / 100 %	41 W	1.8 %	95.6 %
90 / 50 %	34 W	1.5 %	96.2 %
90 / 100 %	45 W	2.0 %	97.3 %

Additional Information	
Product Name	FREQUENCY CONVERTER

Classifications	
UNSPSC	39122001

---

Environmental

---

WEEE Category 5. Small Equipment (No External Dimension More Than 50 cm)

---

---

Categories

---

Drives → Low Voltage AC Drives → Micro Drives → ACS150 - Micro Drive

