



## PRODUCT-DETAILS

# DCS550-S01-0315-05-00-00

DCS550-S01-0315-05-00-00; DC Rectifier ;  
Typecode: DCS550-S01-0315-05-00-00;  
Voltage : 525 V; Current : 315 A; One bridge /  
Rectifier; incl. Panel; Fieldexict

Global Commercial Alias	DCS550-S01-0315-05-00-00
Product ID	3ADT218467R0001
ABB Type Designation	DCS550-S01-0315-05-00-00
	DCS550-S01-0315-05-00-00; DC Rectifier ; Typecode: DCS550-S01-0315-05-00-00;
Catalog Description	Voltage : 525 V; Current : 315 A; One bridge / Rectifier; incl. Panel; Fieldexict

## Ordering

Country of Origin	Poland (PL)
Customs Tariff Number	85044082
Invoice Description	DC Rectifier ; Typecode: DCS550-S01-0315-05-00-00; Voltage : 525 V; Current : 315 A; One bridge / Rectifier; incl. Panel; Fieldexict
Made To Order	No
Minimum Order Quantity	1 piece
Quote Only	No
Selling Unit of Measure	piece

## Dimensions

Product Net Weight	25 kg
Product Net Depth / Length	310 mm
Product Net Height	459 mm
Product Net Width	270 mm

## Technical

Frame Size	F3
------------	----

Additional Information	
Product Name	DCS550 DC Converter Module

Classifications	
UNSPSC	39121007

Environmental	
WEEE Category	Product Not in WEEE Scope

Categories	
Drives → DC Drives → Standard Drives, Modules → DCS550	
Drives → DC Drives → Standard Drives, Modules → DCS550	