

PRODUCT-DETAILS

DCS550-S01-0740-05-01-00

DC Rectifier ; Typecode: DCS550-S01-0740-05-01-00; Voltage : 525 V; Current : 740 A; One bridge / Rectifier; incl. Panel; Fieldexict



General Information

Global Commercial Alias	DCS550-S01-0740-05-01-00
Product ID	3ADT218468R0102
ABB Type Designation	DCS550-S01-0740-05-01-00
	DC Rectifier ; Typecode: DCS550-S01-0740-05-01-00;
Catalog Description	Voltage : 525 V; Current : 740 A; One bridge / Rectifier; incl. Panel; Fieldexict

Ordering

Country of Origin	Germany (DE)
Customs Tariff Number	85044082
Invoice Description	DC Rectifier ; Typecode: DCS550-S01-0740-05-01-00; Voltage : 525 V; Current : 740 A; One bridge / Rectifier; incl. Panel; Fieldexict
Made To Order	No
Minimum Order Quantity	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions	
Product Net Weight	38 kg
Product Net Depth / Length	345 mm
Product Net Height	644 mm
Product Net Width	270 mm

Technical	
Frame Size	F4

Additional Information	
Product Name	DCS550 DC Converter Module

Classifications	
UNSPSC	39121007

Environmental	
WEEE Category	Product Not in WEEE Scope

Categories	
Drives → DC Drives → Standard Drives, Modules → DCS550	



