

PRODUCT-DETAILS

DCT880-W03-0100-04+J404+S500

Thyristor power controller Type:DCT880-W03-0100-04+J404+S500 Voltage:3x110V to 400VAC Legs:3 Current:100A Weight:11kg



General Information

Global Commercial Alias	DCT880-W03-0100-04+J404+S500
Product ID	3ADT218525S1351
ABB Type Designation	DCT880-W03-0100-04+J404+S500
Catalog Description	Thyristor power controller Type:DCT880-W03-0100-04+J404+S500 Voltage:3x110V to 400VAC Legs:3 Current:100A Weight:11kg
Long Description	Thyristor power controller Type:DCT880-W03-0100-04+J404+S500 Voltage:3x110V to 400VAC Legs:3 Current:100A Weight:11kg

Additional Information

ABB Type Designation	DCT880-W03-0100-04+J404+S500
Ambient Air Temperature	32..104 °F 0..40 °C
Analog Inputs	3

Analog Outputs	2
Auxiliary Voltage DC	24 V DC
Country of Origin	Poland (PL)
Customs Tariff Number	85365003
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP00
ETIM 7	EC011564 - Thyristor power controller
ETIM 8	EC011564 - Thyristor power controller
Frame Size	T1
Frequency (f)	50 Hz 60 Hz
Global Commercial Alias	DCT880-W03-0100-04+J404+S500
Gross Weight	11 kg
Invoice Description	Thyristor power controller Type:DCT880-W03-0100-04+J404+S500 Voltage:3x110V to 400VAC Legs:3 Current:100A Weight:11kg
Made To Order	No
Minimum Order Quantity	1 piece
Number of Digital Inputs	6
Number of Digital Outputs	3
Number of Fans	2
	5..95_ % \$
Order Multiple	1 piece
Output Power	69 W
Pollution Degree	2
Power Loss	0.41 W
Product Name	DCT880 AC Controller
Product Net Depth / Length	215 mm
Product Net Height	370 mm
Product Net Weight	11 kg
Product Net Width	270 mm
Product Type	DCT880
Quote Only	No
Rated Input Voltage (U_{IN})	110...415 V AC
Rated Output Current	100 A
Rated Voltage (U_r)	400 V
Selling Unit of Measure	piece
Short Description	DCT880-W03-0100-04+J404+S500
Stocked At (Warehouses)	Ladenburg, Germany Singapore, Singapore
ETIM 9	EC011564 - Thyristor power controller

