

PRODUCT-DETAILS

DCT880-W03-0550-05+J404+S500

Thyristor power controller Type:DCT880-W03-0550-05+J404+S500 Voltage:3x110V to 525VAC Legs:3 Current:550A Weight:38kg



General Information

Global Commercial Alias	DCT880-W03-0550-05+J404+S500
Product ID	3ADT218528S1312
ABB Type Designation	DCT880-W03-0550-05+J404+S500
Catalog Description	Thyristor power controller Type:DCT880-W03-0550-05+J404+S500  Voltage:3x110V to 525VAC Legs:3 Current:550A Weight:38kg
Long Description	Thyristor power controller Type:DCT880-W03-0550-05+J404+S500  Voltage:3x110V to 525VAC Legs:3 Current:550A Weight:38kg

Additional Information

ABB Type Designation	DCT880-W03-0550-05+J404+S500
Ambient Air Temperature	32..104 °F 0..40 °C
Analog Inputs	3

Analog Outputs	2
Auxiliary Voltage DC	24 V DC
Country of Origin	Poland (PL)
Customs Tariff Number	85365003
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP00
ETIM 7	EC011564 - Thyristor power controller
ETIM 8	EC011564 - Thyristor power controller
Frame Size	T4
Frequency (f)	50 Hz 60 Hz
Global Commercial Alias	DCT880-W03-0550-05+J404+S500
Gross Weight	38 kg
Invoice Description	Thyristor power controller Type:DCT880-W03-0550-05+J404+S500 Voltage:3x110V to 525VAC Legs:3 Current:550A Weight:38kg
Made To Order	No
Minimum Order Quantity	1 piece
Number of Digital Inputs	6
Number of Digital Outputs	3
Number of Fans	1
	5..95_ %\$
Order Multiple	1 piece
Output Power	476 W
Pollution Degree	2
Power Loss	1.84 W
Product Name	DCT880 AC Controller
Product Net Depth / Length	352 mm
Product Net Height	644 mm
Product Net Weight	38 kg
Product Net Width	270 mm
Product Type	DCT880
Quote Only	No
Rated Input Voltage ( $U_{IN}$ )	110...500 V AC
Rated Output Current	550 A
Rated Voltage ( $U_r$ )	500 V
Selling Unit of Measure	piece
Short Description	DCT880-W03-0550-05+J404+S500
Stocked At (Warehouses)	Ladenburg, Germany Singapore, Singapore
ETIM 9	EC011564 - Thyristor power controller

