

PRODUCT-DETAILS

DCT880-W03-0890-05+J404

Thyristor power controller ; Type:DCT880-W03-0890-05+J404 Voltage: 3x110V to 525VAC; Legs:3; Current: 970A; Weight: 110kg;



General Information

Global Commercial Alias	DCT880-W03-0890-05+J404
Product ID	3ADT218529S1312
ABB Type Designation	DCT880-W03-0890-05+J404
Catalog Description	Thyristor power controller ; Type:DCT880-W03-0890-05+J404 Voltage: 3x110V to 525VAC; Legs:3; Current: 970A; Weight: 110kg;
Long Description	Thyristor power controller ; Type:DCT880-W03-0890-05+J404 Voltage: 3x110V to 525VAC; Legs:3; Current: 970A; Weight: 110kg;

Additional Information

ABB Type Designation	DCT880-W03-0890-05+J404
Ambient Air Temperature	32...104 °F 0...40 °C
Analog Inputs	3

Analog Outputs	2
Auxiliary Voltage DC	24 V DC
Country of Origin	Poland (PL)
Customs Tariff Number	85365003
Degree of Protection	acc. to IEC 60529, IEC 60947-1, EN 60529 Auxiliary Terminals IP00
ETIM 7	EC011564 - Thyristor power controller
ETIM 8	EC011564 - Thyristor power controller
Frame Size	T5
Frequency (f)	50 Hz 60 Hz
Global Commercial Alias	DCT880-W03-0890-05+J404
Gross Weight	110 kg
Invoice Description	Thyristor power controller ; Type:DCT880-W03-0890-05+J404 Voltage: 3x110V to 525VAC; Legs:3; Current: 970A; Weight: 110kg;
Made To Order	No
Minimum Order Quantity	1 piece
Number of Digital Inputs	6
Number of Digital Outputs	3
Number of Fans	1
	5..95_ %\$
Order Multiple	1 piece
Output Power	770 W
Pollution Degree	2
Power Loss	3.5 W
Product Name	DCT880 AC Controller
Product Net Depth / Length	372 mm
Product Net Height	750 mm
Product Net Weight	110 kg
Product Net Width	270 mm
Product Type	DCT880
Quote Only	No
Rated Input Voltage (U_{IN})	110...500 V AC
Rated Output Current	890 A
Rated Voltage (U_r)	500 V
Selling Unit of Measure	piece
Short Description	DCT880-W03-0890-05+J404
Stocked At (Warehouses)	Ladenburg, Germany Singapore, Singapore
ETIM 9	EC011564 - Thyristor power controller

