

PRODUCT-DETAILS

ACS550-01-04A1-4

ACS550-01-04A1-4,4.1A,380V,IP21



General Information

Global Commercial Alias	ACS550-01-04A1-4
Product ID	3AUA0000003386-D
ABB Type Designation	ACS550-01-04A1-4
Catalog Description	ACS550-01-04A1-4,4.1A,380V,IP21
Long Description	ACS550-01-04A1-4,4.1A,380V,IP21

Ordering

Country of Origin	China (CN)
Customs Tariff Number	85044099
Invoice Description	ACS550-01-04A1-4,4.1A,380V,IP21
Made To Order	No
Minimum Order Quantity	1 piece
Order Multiple	1 piece
Quote Only	No
Selling Unit of Measure	piece

Dimensions

Product Net Weight	6.17 kg
Product Net Depth / Length	465 mm
Product Net Height	365 mm
Product Net Width	225 mm
Package Level 1 Depth / Length	490 mm
Package Level 1 Height	400 mm
Package Level 1 Width	240 mm

Technical

Number of Phases	3
Degree of Protection	IP21
Enclosure Type NEMA	Type1
Frequency (f)	47.5 ... 63 Hz
Frame Size	R1
Input Voltage (U_{in})	380 ... 480 V
Mounting Type	Wall-mounted_NO UNIT\$
Output Current, Heavy-Duty Use (I_{HD})	3.3 A
Output Current, Normal Use (I_n)	4.1 A
Output Power, Heavy-Duty Use (P_{HD})	1.1 kW
Output Power, Normal Use (P_n)	1.5 kW
Efficiency Level	IE2
Complete Drive Module Efficiency (61800-9-2)	

Operating Point Frequency / Current	Absolute Loss	Relative Loss	Efficiency
0 / 25 %	31 W	1.1 %	82.7 %
0 / 50 %	35 W	1.2 %	89.3 %
0 / 100 %	44 W	1.5 %	92.5 %
50 / 25 %	33 W	1.2 %	90.5 %
50 / 50 %	38 W	1.3 %	94.2 %
50 / 100 %	49 W	1.7 %	95.8 %
90 / 50 %	41 W	1.4 %	96.4 %
90 / 100 %	54 W	1.9 %	97.4 %

Additional Information

Product Name	Frequency Converter
--------------	---------------------

Classifications

UNSPSC	39122001
--------	----------

Environmental	
WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-01 - Wall-mounted drive

