



## PRODUCT-DETAILS

# ACS550-U1-178A-2

ACS550-U1-178A-2,60HP/178AMPS,60HP,208-240V +-10%,IP21-NEMA1,R6,48-63Hz,Dir Connect,Bot/Side Conduit

### General Information

Global Commercial Alias	ACS550-U1-178A-2
Product ID	3AUA0000003769
ABB Type Designation	ACS550-U1-178A-2
EAN	6438177208594
Catalog Description	ACS550-U1-178A-2,60HP/178AMPS,60HP,208-240V +-10%,IP21-NEMA1,R6,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-178A-2

### Ordering

Core Credit	0.00
Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-178A-2,60HP/178AMPS,60HP,208-240V +-10%,IP21-NEMA1,R6,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

### Dimensions

Product Net Weight	0 kg
--------------------	------

### Technical

Number of Phases	3
Frequency (f)	48...63 Hz
Frame Size	R6
Input Voltage ( $U_{in}$ )	208...240+-10% V

### Additional Information

Product Main Type	ACS550-U1
Product Name	-

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US