



PRODUCT-DETAILS

ACS550-U1-07A5-2+B055

ACS550-U1-07A5-

2+B055,2HP/7.5AMPS,2HP,208-240V +-

10%,IP54-NEMA12,R1,48-63Hz,Dir

Connect,Bot/Side Conduit

General Information

Global Commercial Alias	ACS550-U1-07A5-2+B055
Product ID	3AUA0000004193
ABB Type Designation	ACS550-U1-07A5-2+B055
EAN	6438177206828
Catalog Description	ACS550-U1-07A5-2+B055,2HP/7.5AMPS,2HP,208-240V +-10%,IP54-NEMA12,R1,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-07A5-2+B055

Ordering

Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-07A5-2+B055,2HP/7.5AMPS,2HP,208-240V +-10%,IP54-NEMA12,R1,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Number of Phases	3
Frequency (f)	48...63 Hz
Frame Size	R1
Input Voltage (U _{in})	208...240+-10% V

Additional Information

Product Main Type	ACS550-U1
Product Name	-

Environmental

WEEE Category	5. Small Equipment (No External Dimension More Than 50 cm)
---------------	--

Categories

Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US