



PRODUCT-DETAILS

ACS550-U1-088A-2+B055

ACS550-U1-088A-

2+B055,30HP/88AMPS,30HP,208-240V +-10%,IP54-NEMA12,R4,48-63Hz,Dir

Connect,Bot/Side Conduit

General Information

Global Commercial Alias	ACS550-U1-088A-2+B055
Product ID	3AUA0000004212
ABB Type Designation	ACS550-U1-088A-2+B055
EAN	6438177206705
Catalog Description	ACS550-U1-088A-2+B055,30HP/88AMPS,30HP,208-240V +-10%,IP54-NEMA12,R4,48-63Hz,Dir Connect,Bot/Side Conduit
Long Description	ACS550-U1-088A-2+B055

Ordering

Core Credit	0.00
Country of Origin	United States (US)
Customs Tariff Number	85044080
Invoice Description	ACS550-U1-088A-2+B055,30HP/88AMPS,30HP,208-240V +-10%,IP54-NEMA12,R4,48-63Hz,Dir Connect,Bot/Side Conduit
Made To Order	No
Minimum Order Quantity	1 EA
Order Multiple	1 EA
Quote Only	No
Selling Unit of Measure	each

Dimensions

Product Net Weight	0 kg
--------------------	------

Technical

Number of Phases	3
Frequency (f)	48...63 Hz
Frame Size	R4
Input Voltage (U _{in})	208...240+-10% V

Additional Information

Product Main Type	ACS550-U1
Product Name	-

Environmental	
WEEE Category	4. Large Equipment (Any External Dimension More Than 50 cm)

Categories
Drives → Low Voltage AC Drives → Legacy AC Drives → ACS550-U1 - Wall-mounted base drive US